




# CASTERS ねじ込みキャスター -軽荷重-



許容荷重  
250~600N  
ねじ込み

◎ CADデータフォルダ名: 47\_Casters



本体タイプ	型式	車輪材質	H	M (並目)	b	t	ℓ	r	B	e	許容荷重(N)	質量(g)	¥基準単価												
ねじ式タイプ	CSTUN	R (ゴム) N (ナイロン)	50A	12	21	4.8	35	53	28	27	500	600	600	350	335	265	290	270	448	350	650	520			
			50B	16	23	40	35	61	25		40	500	700	600	400	390	285	390	320	480	535	495	770	480	
			65A	12	21	40	35	66	25		40	600	800	700	500	430	315	440	340	539	595	865	550	800	570
			65B	16	23	40	35	66	25		40	600	800	700	500	430	315	440	340	539	595	865	550	800	570
			75A	12	21	40	35	66	25		40	600	800	700	500	430	315	440	340	539	595	865	550	800	570
75B	16	23	40	35	66	25	40	600	800	700	500	430	315	440	340	539	595	865	550	800	570				
ねじ式ストッパ付タイプ	CSTUNS	U (ウレタン) E (エラストマー)	50A	12	21	4.8	35	67	28	27	500	600	600	350	360	320	325	325	560	585	745	650			
			50B	16	23	40	35	68	25		40	500	700	600	400	375	345	370	370	588	670	880	575		
			65A	12	21	40	35	68	25		40	600	800	700	500	485	360	390	390	644	730	985	675		
			65B	16	23	40	35	68	25		40	600	800	700	500	485	360	390	390	644	730	985	675		
			75A	12	21	40	35	68	25		40	600	800	700	500	485	360	390	390	644	730	985	675		
75B	16	23	40	35	68	25	40	600	800	700	500	485	360	390	390	644	730	985	675						

