


📄カタログ規格外品はこちら 📄P.137

■キリ欠き穴タイプ

■丸穴タイプ



RoHS10

型式			M材質	H硬度	T厚さ(T)公差								キリ欠き穴タイプ 加工条件 Ⓜ f≧3 Ⓜ a≧3 Ⓜ m≧3 Ⓜ n≧3	
キリ欠き穴1コ	キリ欠き穴2コ	キリ欠き穴3コ			0.05	0.1	0.15	0.2	0.3	0.5	1.0	2.0		
ASAFR	ASFFR	ASCFR	SPCC相当	—	—	±0.03	—	±0.03	±0.04	±0.06	±0.11	±0.17	—	
ASAFB	ASFFB	ASCFB	黄銅 (C2801P又はC2680P)	—	±0.005	±0.02	—	±0.03	±0.04	±0.05	±0.08	±0.12	±0.15	
ASAFS	ASFFS	ASCFS	T=0.05~1.0 SUS304H T=2.0・3.0 SUS304	370~430HV —	±0.005	±0.02	±0.025	±0.03	±0.035	±0.04	±0.05	±0.20	±0.25	

キリ欠き穴1コ

キリ欠き穴2コ

キリ欠き穴3コ

型式			指定1mm単位		選択	指定0.1mm単位				P
Type	A	B	A	B	T	Q	E	C		
SPCC相当	黄銅	SUS304 (H)	10~150	10~150	(0.05) 0.1 (0.15)	3~31	Q/2+3~	0 B-(Q/2+3)		📌穴1コタイプ は指定不要
穴1コ	ASAFR	ASAFB	ASAFS		0.2 0.3 0.5					
穴2コ	ASFFR	ASFFB	ASFFS	16~200	1.0 2.0 (3.0)					
穴3コ	ASCFR	ASCFB	ASCFS	10~200						Q+3~

📌T (0.05), (3.0)はSPCC相当材で指定できません。📌T (0.15)はSUS304Hのみ。

Order
注文例

型式

— A — B — T — Q — E — C — P

ASFFB — A100 — B25 — T1.0 — Q12 — E15 — C12 — P70

型式			M材質	H硬度	T厚さ(T)公差								丸穴タイプ加工条件			
丸穴1コ	丸穴2コ	丸穴3コ			0.05	0.1	0.15	0.2	0.3	0.5	1.0	2.0			3.0	
ASACR	ASFCR	ASCCR	SPCC相当	—	—	±0.03	—	±0.03	±0.04	±0.06	±0.11	±0.17	—	Ⓣ≥2	Ⓜ≥2	
ASACB	ASFCB	ASCCB	黄銅 (C2801P又はC2680P)	—	±0.005	±0.02	—	±0.03	±0.04	±0.05	±0.08	±0.12	±0.15	Ⓣ≥2	Ⓜ≥2	
ASACS	ASFCS	ASCCS	T=0.05~1.0 T=2.0・3.0	SUS304H SUS304	370~430HV —	±0.005	±0.02	±0.025	±0.03	±0.035	±0.04	±0.05	±0.20	±0.25	Ⓣ≥2	

丸穴1コ

丸穴2コ

丸穴3コ

型式			指定1mm単位		選択	指定0.1mm単位				P
Type	A	B	A	B	T	D	E	C		
SPCC相当	黄銅	SUS304 (H)	10~150	10~150	(0.05) 0.1 (0.15)	3~100	D/2+2~	D/2+2 ~ B-(D/2+2)		📌穴1コタイプ は指定不要
穴1コ	ASACR	ASACB	ASACS		0.2 0.3 0.5					
穴2コ	ASFCR	ASFCB	ASFCs	15~200	1.0 2.0 (3.0)					
穴3コ	ASCCR	ASCCB	ASCCS	10~200						D+2~

📌T (0.05), (3.0)はSPCC相当材で指定できません。📌T (0.15)はSUS304Hのみ。

Order
注文例

型式

— A — B — T — D — E — C — P

ASACR — A50 — B25 — T0.1 — D7.5 — E25 — C11
ASCCS — A120 — B15 — T3.0 — D10 — E15 — C7 — P45

Delivery
出荷日

1 日日出荷

📄ストーク T 当日出荷

200円/1本

📄注文締切

正午迄 📄P.134

Price
価格

■数量スライド価格 (📌1円未満切り捨て) P.133

数量区分	標準対応				個別対応	
	小口		大口		大口	
数 量	1~4	5~9	10~19	20~49	50~150	151~300
値引率	基準単価	10%	20%	30%	35%	39%
出荷日	通常				+5日	+8日

📌表示数量超えはWOSにてご確認ください。
📌標準対応大口以上はストーク対応なし

■キリ欠き穴・丸穴 1コタイプ												
A	B	¥基準単価										
		ASAFR・ASACR			ASAFB・ASACB				ASAFS・ASACS			
		T0.1～0.5	T1.0	T2.0	T0.05	T0.1～0.5	T1.0	T2.0～3.0	T0.05	T0.1～0.5	T1.0	T2.0～3.0
10～50	10～ 50	570	570	780	710	710	860	960	590	590	750	840
	51～100	770	790	810	1,100	910	920	1,080	930	760	800	900
	101～150	790	810	820	1,280	930	950	1,220	1,070	790	800	1,030
51～70	10～ 50	620	620	770	790	790	900	990	750	740	760	890
	51～100	780	790	800	1,040	910	930	1,170	1,030	780	840	1,110
	101～150	810	810	820	1,410	940	980	1,350	1,210	830	920	1,170
71～100	10～ 50	620	620	800	850	850	910	1,070	920	750	800	1,050
	51～100	790	800	810	1,050	930	960	1,290	1,040	810	860	1,200
	101～150	810	820	830	1,590	970	1,020	1,530	1,330	880	960	1,290
101～130	10～ 50	790	800	810	1,060	930	960	1,110	1,000	780	790	1,060
	51～100	800	810	820	1,390	950	1,010	1,390	1,250	820	870	1,250
	101～150	820	820	840	1,760	1,010	1,060	1,720	1,610	880	960	1,550
131～150	10～ 50	790	800	810	1,110	930	960	1,160	1,040	800	810	1,090
	51～100	800	810	830	1,470	970	1,020	1,480	1,270	870	890	1,270
	101～150	820	840	860	1,920	1,020	1,090	1,850	1,590	890	970	1,520

¥基準単価												
A	B	ASFFR・ASFCR			ASFFB・ASFCB				ASFFS・ASFCs			
		T0.1~0.5	T1.0	T2.0	T0.05	T0.1~0.5	T1.0	T2.0~3.0	T0.05	T0.1~0.5	T1.0	T2.0~3.0
15～50	10～50	650	850	900	700	800	900	1,170	750	750	880	1,030
	51～100	950	960	960	1,290	1,010	1,030	1,310	1,160	860	930	1,150
	101～150	960	970	980	1,490	1,020	1,040	1,470	1,300	890	960	1,290
51～70	10～50	750	930	940	830	850	1,000	1,230	840	840	880	1,070
	51～100	880	940	970	960	960	1,020	1,410	980	870	950	1,230
	101～150	960	970	1,000	1,610	1,030	1,050	1,590	1,430	890	1,010	1,390
71～100	10～50	750	930	940	850	850	1,020	1,310	850	850	920	1,150
	51～100	900	960	990	980	980	1,040	1,550	990	880	950	1,360
	101～150	970	970	1,010	1,820	1,040	1,090	1,810	1,630	900	1,060	1,580
101～130	10～50	950	960	960	1,320	1,030	1,030	1,410	1,170	870	960	1,230
	51～100	960	970	1,010	1,660	1,050	1,070	1,700	1,480	900	1,020	1,480
	101～150	970	970	1,020	2,070	1,080	1,120	2,060	1,840	930	1,130	1,810
131～150	10～50	950	960	1,000	1,370	1,030	1,030	1,470	1,220	890	970	1,290
	51～100	960	970	1,020	1,780	1,050	1,070	1,810	1,580	930	1,020	1,580
	101～150	970	1,000	1,080	2,200	1,080	1,150	2,220	2,020	980	1,130	1,940
151～200	10～50	1,370	1,410	1,520	3,030	1,490	1,580	3,050	3,250	1,580	1,820	3,120
	51～100	1,390	1,430	1,540	3,210	1,580	1,670	3,220	3,370	1,640	1,880	3,220
	101～150	1,410	1,450	1,560	3,250	1,600	1,690	3,250	3,590	1,750	2,000	3,420
	151～200	1,470	1,510	1,620	3,370	1,660	1,750	3,360	3,810	1,860	2,120	3,620

■キリ欠き穴・丸穴 3コタイプ												
A	B	¥基準単価										
		ASCFR・ASCCR			ASCFB・ASCCB				ASCFs・ASCCS			
		T0.1~0.5	T1.0	T2.0	T0.05	T0.1~0.5	T1.0	T2.0~3.0	T0.05	T0.1~0.5	T1.0	T2.0~3.0
15~ 50	10~ 50	890	920	920	1,040	990	1,010	1,180	950	850	880	1,060
	51~100	960	970	970	1,310	1,020	1,040	1,320	1,190	880	950	1,180
	101~150	970	980	990	1,510	1,030	1,050	1,490	1,340	910	980	1,320
51~ 70	10~ 50	890	920	930	1,090	990	1,010	1,240	1,000	840	880	1,100
	51~100	910	940	960	1,320	1,000	1,020	1,420	1,200	870	950	1,260
	101~150	970	980	1,010	1,620	1,040	1,070	1,600	1,470	910	1,030	1,430
71~100	10~ 50	900	930	930	1,170	990	1,010	1,320	1,070	850	920	1,180
	51~100	920	950	980	1,460	1,010	1,040	1,560	1,310	880	950	1,390
	101~150	980	980	1,020	1,840	1,050	1,100	1,820	1,670	930	1,080	1,620
101~130	10~ 50	960	970	970	1,330	1,040	1,040	1,420	1,200	890	980	1,260
	51~100	970	980	1,020	1,680	1,070	1,080	1,720	1,520	930	1,050	1,520
	101~150	980	980	1,030	2,090	1,090	1,130	2,080	1,890	950	1,160	1,850
131~150	10~ 50	960	970	1,010	1,380	1,040	1,040	1,490	1,250	910	990	1,320
	51~100	970	980	1,030	1,800	1,070	1,080	1,820	1,620	950	1,050	1,620
	101~150	980	1,020	1,090	2,230	1,090	1,160	2,250	2,070	1,000	1,160	1,990
151~200	10~ 50	1,470	1,530	1,630	3,270	1,600	1,700	3,290	3,490	1,690	1,960	3,360
	51~100	1,490	1,550	1,650	3,450	1,690	1,790	3,460	3,610	1,750	2,020	3,460
	101~150	1,520	1,580	1,680	3,490	1,710	1,810	3,490	3,830	1,860	2,140	3,660
	151~200	1,580	1,640	1,740	3,610	1,770	1,870	3,600	4,030	1,960	2,250	3,840

33
カラー・
シム