







STRIPPER GUIDE PINS - REMOVABLE TYPE -

ストリッパガイドピン
-着脱タイプ-

追加工価格も数量スライド適用 P.43




MxL Pitch	D ₁	R	B	型式		L	¥基準単価 SGPR SGOR		
				Type	D		30 40 50	60 70	
M5×12 P0.8	13	1.0	8	SGPR SGOR	8	30 40 50	60 70	460 520	
	16				10	30 40 50 60	70 80	520 590	
	20	1.5	10		13	40 50 60	70 80	540 650	
	23				16	40 50 60	70 80 90 100	610 720	
	27	2.0	13		20	50 60 70 80	90 100	690 820	
	32				25	60 70 80	90 100	730 940	
M6×15 P1.0	20	1.5	10		13	40 50 60	70 80	630 750	
	23				16	40 50 60	70 80 90 100	830 980	
	27	2.0	13		20	50 60 70 80	90 100	770 930	
	32				25	60 70 80	90 100	900 1,070	
	27	2.0	13		20	50 60 70 80	90 100	1,060 1,230	
	32				25	60 70 80	90 100	950 1,130	
M8×20 P1.25	27	2.0	13		20	50 60 70 80	90 100	1,100 1,290	
	32				25	60 70 80	90 100	1,270 1,500	



STRIPPER GUIDE PINS - BOTH SIDED TAPPED TYPE -

ストリッパガイドピン
-着脱・両タップタイプ-

追加工価格も数量スライド適用 P.43



MxL Pitch	N Pitch	L	D ₁	R	T	B	型式		L 指定5mm単位	¥基準単価 1~9本	
							Type	D			
M4×12 P0.7	M4 P0.7	8~13	12	1.0	3	8	SGPW	8	25~70	990	
								10			
	M5 P0.8	10~15	17	1.5	23	10		13	30~75	1,060	
								16			
	M6×15 P1.0	16~21	27	2.0	32	13		20	60~120	1,390	
								25			



Alterations	Code	Spec.	¥/1Code
	LC	全長変更 30≤LC<L 指定0.5mm単位	500
	BC	B寸法変更 5≤BC<B 指定1mm単位 Mタップ深さは(B-BC)分短くなります。	200

