

数量区分	標準対応				個別対応 大口
数 量	1～4	5～19	20～29	30～50	51～
値引率	基準単価	5%	10%	15%	お見積り

材質 **SKH51**

材質 **NAK80**

ブロックコアピン
入れ子


材質 **SKH51**

材質 **NAK80**

型 式	W	P	¥ 基準単価 1~4本						
			1.00~1.99	2.00~3.00	3.01~5.00	5.01~10.00	10.01~15.00	15.01~20.00	
BCSN-1AR	1.00~ 1.99	8,830	9,500	10,080	10,500	—	—		
	2.00~ 3.00	9,500	5,550	5,550	5,390	5,410	4,560		
	3.01~ 5.00	10,080	5,550	4,590	4,310	4,400	4,560		
	5.01~10.00	10,500	5,390	4,310	4,070	4,150	4,730		
	10.01~15.00	—	5,410	4,400	4,150	4,650	5,140		
BCSN-1BR	15.01~20.00	—	4,560	4,560	4,730	5,140	5,730		
	1.00~ 1.99	9,280	9,950	10,530	10,950	—	—		
	2.00~ 3.00	9,950	6,000	6,000	5,840	5,860	5,010		
	3.01~ 5.00	10,530	6,000	5,040	4,760	4,850	5,010		
	5.01~10.00	10,950	5,840	4,760	4,520	4,600	5,180		
BCSN-2AR	10.01~15.00	—	5,860	4,850	4,600	5,100	5,590		
	15.01~20.00	—	5,010	5,010	5,180	5,590	6,180		
	1.00~ 1.99	9,680	10,350	10,930	11,350	—	—		
	2.00~ 3.00	10,350	6,400	6,400	6,240	6,260	5,410		
	3.01~ 5.00	10,930	6,400	5,440	5,160	5,250	5,410		
BCSN-2BR	5.01~10.00	11,350	6,240	5,160	4,920	5,000	5,580		
	10.01~15.00	—	6,260	5,250	5,000	5,500	5,990		
	15.01~20.00	—	5,410	5,410	5,580	5,990	6,580		
	1.00~ 1.99	9,980	10,650	11,230	11,650	—	—		
	2.00~ 3.00	10,650	6,700	6,700	6,540	6,560	5,710		
BCSN-3AR	3.01~ 5.00	11,230	6,700	5,740	5,460	5,550	5,710		
	5.01~10.00	11,650	6,540	5,460	5,220	5,300	5,880		
	10.01~15.00	—	6,560	5,550	5,300	5,800	6,290		
	15.01~20.00	—	5,710	5,710	5,880	6,290	6,880		
	BCSN-4AR	1.00~ 1.99	9,980	10,650	11,230	11,650	—	—	
2.00~ 3.00		10,650	6,700	6,700	6,540	6,560	5,710		
3.01~ 5.00		11,230	6,700	5,740	5,460	5,550	5,710		
5.01~10.00		11,650	6,540	5,460	5,220	5,300	5,880		
10.01~15.00		—	6,560	5,550	5,300	5,800	6,290		
BCSN-4BR	15.01~20.00	—	5,710	5,710	5,880	6,290	6,880		


SPHD —

BCSSN —



R加工数	Shape	R位置			
		①左上	②右上	③左下	④右下
1ヶ所	1AR	①	—	—	—
	1BR	—	②	—	—
	2AR	①	②	—	—
2ヶ所	2BR	①	—	③	—
	2CR	①	—	—	④
	2DR	—	②	—	④
3ヶ所	3AR	①	②	③	—
	3BR	①	②	—	④
4ヶ所	4R	①	②	③	④

❗ R加工は全長にわたるため、
フランジ部側面に内Rの溝がつきます。



型 式		指定0.01mm単位			R
Type	Shape	L	P	W	
SPHD— (SKH51)	1AR	10.00~*70.00	1.00~ 1.99	1.00~10.00	0.1
	2AR				
	2BR				
BCSSN— (NAK80)	2CR		2.00~10.00	1.00~20.00	0.15
	3AR				0.2
	4R		10.01~20.00	2.00~20.00	

型 式		指定0.01mm単位			R	H
Type	Shape	L	P	W		
BCSH— (SKH51)	1AR	10.00~70.00	1.00~ 1.99	1.00~10.00	0.1	4
	1BR					
	2AR		2.00~10.00	1.00~20.00		
	2BR					
2CR						
2DR	10.01~20.00				2.00~20.00	
3AR						
3BR						
4R						
BCSN— (NAK80)						6



Order
注文例

型 式		L	P	W	R	H (BCSH BCSN)
Type	Shape					
BCSH-1AR		20.00	P3.20	W3.00	R0.2	H6

■精度基準：P.591

Delivery
出荷日

3 日日出荷

Price
価格 P.594Alterations
追加工 P.591