


FIXING KEYS FOR PUNCHES WITH KEY GROOVES
キー溝付パンチ用固定キー




ボルト	D	d	T	型式	
				Type	No.
M4	10	4.2	3	PSKB	4
			4.5		4-4.5
	12	5.2	3		5
			4.5		5-4.5
	14	6.2	3		6
			4.5		6-4.5
M4	10	4.2	3	PSKBH	4
			4.5		4-4.5
	12	5.2	3		5
			4.5		5-4.5
	14	6.2	3		6
			4.5		6-4.5

型式	M 材質	H 硬度
PSKS	S45C	45~55HRC
PSKJ	SKS3	58~62HRC

PSKS Dimensions: $D=10\text{mm}$, $d=4.5\text{mm}$, $t=2.5\text{mm}$, $\phi d=8\text{mm}$, $B=0.2\text{mm}$, $C=0.3\text{mm}$.



PSKJ Dimensions: $D=12\text{mm}$, $d=5.5\text{mm}$, $t=3\text{mm}$, $\phi d=8\text{mm}$, $B=0.2\text{mm}$, $C=0.3\text{mm}$.



ボルト	B	C	d	P	型式	Type	T	指定1mm単位
M4	11	6	4.2	10	PSKW	4	3	21~50
			5.2	—		5	4.5	31~60



KEYS
廻り止めキー



型式	Bh9	L	H許容差	C
KED	2 0	10 15 20	2 0	0.16~0.25
	3 -0.025	10 15 20 25 30	3 -0.025	
	4 0	10 12 15 16 18 20 25 30 35 40 45 50	4 0	
	5 -0.030	10 12 15 16 18 20 25 30 35 40 45 50	5 -0.030	
	6 0	10 12 15 16 18 20 25 30 35 40 45 50 55 60	6 0	0.25~0.40
	7 0	15 20 25 30 35 40 45 50 60	7 -0.036	
	8 -0.036	15 16 18 20 25 30 35 40 45 50 55 60 70 80	8 0	
	10 0	15 18 20 25 30 35 40 45 50 55 60 70 80	10 0	0.40~0.60
	12 0	20 25 30 35 40 45 50 55 60 70 80	12 0	
	14 0	30 35 40 45 50 55 60 70 80 90	14 0	
	15 -0.043	30 35 40 45 50 55 60 70 80 90	15 0	
	16 0	40 45 50 55 60 70 80 90 100	16 0	
	18 0	40 45 50 55 60 70 80 90 100 110	18 0	



追加工	記号	詳細
全長	LC	LC = 指定1mm単位 B 2 5~20 3 6~30 4 8~50 5 8~50 6 10~60 7 15~60 8 15~80 10 15~80 12 20~80 14 25~90 15 25~90 16 35~100 18 35~110