



CAVITY INSERT WEDGE SPACERS
入れ子止め用スペーサ


追加加工価格も数量スライド適用 ㊦ P.49



型 式	材質	硬度
ICSS	SKS3	53～56HRC
ICHS	HPM2T相当	37～41HRC



型 式	材質	硬度
IUSS	SKS3	53～56HRC
IUHS	HPM2T相当	37～41HRC



型 式		T	L 指定10mm単位	A
Type	W			
ICSS (SKS3)	5	15	30～100	1
		20		
		25		
		30		
		35		
		40	30～180	
		45		
		50		
		60		
		70		
80	3			
ICHS (HPM2T相当)	10	20	40～180	5
		25		
		30		
		35		
		40		
		45		
		50		
		60		
		70		
		80		

型 式		T	L 指定10mm単位	A	入れ子止め 組み合わせ例 W-T	
Type	W					
IUSS (SKS3)	5	20	20～100	1	10-20	
		15			6-15	
		20			10-20	
		25			10-25	
IUHS (HPM2T相当)	10	25	30～180	3	10-30	
		30			8-15	
		15			8-20	
	12	20	30～180		5	8-20
		25				8-25

 Order
注文例

型 式 - T - L - A
ICSS5 - 20 - L100 - A5

 Delivery
出荷日

5 日日出荷

 ストック B 3日日出荷 300円/1本 PM 8:00迄

 ご注文締切

 P48

 Price
価格

■数量スライド価格 (㊦1円未満切り捨て) P47

数量区分	標準対応	個別対応 大口
数 量	1～9 10～19 20～49 50～	50～
値引率	基準単価 5% 10% お見積り	


㊦表示数量超えはWOSIにてご確認ください。

型 式	W	T	L	¥ 基準単価 1～9本							
Type				L30・40	L50・60	L70・80	L90・100	L110・120	L130～150	L160～180	
ICSS (SKS3)	5	15		1,850	2,380	2,960	3,340	—	—	—	
		20		1,920	2,450	3,090	3,470	—	—	—	
		25		2,210	2,740	3,470	3,990	5,010	6,050	7,860	
		30		2,310	2,970	3,660	4,170	5,420	6,390	8,290	
		35		2,660	3,260	3,980	4,820	5,950	6,970	9,030	
		40		2,950	3,560	4,280	5,320	6,490	7,520	9,730	
		45		3,490	3,640	4,410	5,410	6,620	7,780	10,050	
		50		3,630	3,790	4,590	5,630	6,920	8,120	10,490	
		60		3,710	3,880	4,690	5,760	7,070	8,300	10,720	
		70		4,090	4,270	5,170	6,350	7,780	9,170	11,820	
	10	80		4,500	4,690	5,700	6,980	8,560	10,120	13,020	
		20		1,970	2,510	3,150	3,540	4,520	5,690	7,240	
		25		2,140	2,640	3,340	3,850	4,770	6,030	7,660	
		30		2,230	2,870	3,520	4,020	5,160	6,350	8,080	
		35		2,560	3,140	3,830	4,630	5,660	6,900	8,770	
		40		2,830	3,420	4,120	5,110	6,170	7,420	9,440	
		45		3,340	3,500	4,230	5,190	6,300	7,660	9,740	
		50		3,480	3,640	4,410	5,400	6,570	7,990	10,160	
		60		3,550	3,720	4,500	5,520	6,720	8,160	10,370	
		70		3,910	4,090	4,950	6,080	7,390	8,980	11,420	
ICHS (HPM2T相当)	5	80		4,310	4,500	5,460	6,680	8,130	9,880	12,560	
		15		1,650	2,140	2,660	3,000	—	—	—	
		20		1,730	2,210	2,790	3,120	—	—	—	
		25		1,990	2,470	3,130	3,580	4,690	5,150	7,620	
		30		2,080	2,680	3,300	3,750	5,070	5,460	8,020	
		35		2,390	2,940	3,570	4,320	5,540	5,970	8,650	
		40		2,650	3,210	3,850	4,780	6,020	6,470	9,300	
		45		2,710	3,290	3,980	4,870	6,180	6,710	9,600	
		50		2,820	3,440	4,170	5,100	6,450	7,040	10,020	
		60		3,020	3,680	4,340	5,310	6,710	7,200	10,220	
	10	70		3,490	4,240	4,860	5,960	7,500	7,980	11,220	
		80		4,020	4,880	5,450	6,690	8,380	8,840	12,300	
		20		1,770	2,250	2,840	3,190	4,070	5,130	6,520	
		25		1,910	2,380	3,010	3,460	4,290	5,420	6,900	
		30		2,000	2,580	3,170	3,620	4,650	5,720	7,280	
		35		2,300	2,820	3,430	4,160	5,090	6,200	7,880	
		40		2,540	3,080	3,690	4,590	5,550	6,670	8,490	
		45		2,600	3,150	3,820	4,680	5,700	6,900	8,770	
		50		2,700	3,300	4,000	4,900	5,950	7,210	9,180	
		60		2,890	3,520	4,160	5,100	6,200	7,370	9,360	
IUHS (HPM2T相当)	12	70		3,330	4,050	4,660	5,710	6,940	8,100	10,310	
		80		3,840	4,670	5,220	6,400	7,780	8,910	11,340	


型 式	W	T	L	¥ 基準単価 1～9本							
Type				L20	L30・40	L50・60	L70・80	L90・100	L110・120	L130～150	L160～180
IUSS (SKS3)	5	20		1,950	1,990	2,540	3,180	3,600	—	—	—
		9		1,870	1,890	2,410	3,020	3,420	—	—	—
		20			2,030	2,570	3,220	3,640	4,620	5,780	7,360
		25			2,130	2,700	3,380	3,830	4,860	6,070	7,730
		30			2,250	2,820	3,510	3,950	4,970	6,190	7,880
	10	15		—	2,010	2,560	3,220	3,640	—	—	—
		20			2,130	2,700	3,380	3,830	4,860	6,070	7,730
		25			2,180	2,760	3,430	3,880	4,910	6,120	7,790
		20		1,740	1,790	2,140	3,100	3,490	—	—	—
		9		1,650	1,690	2,140	2,690	3,030	—	—	—
IUHS (HPM2T相当)	10	20			1,810	2,300	2,880	3,250	4,100	5,130	6,530
		25			1,900	2,430	3,030	3,430	4,320	5,410	6,890
		30			2,030	2,540	3,150	3,550	4,440	5,540	7,060
		15		—	1,800	2,300	2,870	3,250	—	—	—
		20			1,900	2,420	3,030	3,430	4,320	5,400	6,890
	12	25			1,970	2,480	3,100	3,490	4,380	5,460	6,950


 Alterations
追加加工

型 式 - T - L - A - (MC)
ICSS5 - 20 - L100 - A5 - MC

Alteration	Code	Spec.	¥/1Code
	MC	W寸法指定側にタップ加工します。 W M 5 3 10 5 L l 30・40 7.5 50～100 10 110～180 15	600

 Example
使用例





・追加加工 MC 適用の場合、入れ子止めとしてもご利用いただけます。