



型式			A	B	a	b	d	H	T	(Q)	M	eH7		l	a1	b1
Type	D _{k6}											eH7				
MGH	20	+0.002 -0.011	74	44	56	30	6.6	30	15	42	8	6	+0.012 0	56	28	15
	25		84	48	66		9		20	46		8		66	33	
	32	+0.003 -0.013	100	58	76	36	11	40		56			+0.015 0	76	38	18
	38		130	75	100	44		50		73				100	50	22
	50		155	90	125	60	14	65	25	87	10			125	62.5	30
	60	+0.004 -0.014	190	120	150	80	18	75	30	116		13	+0.018 0	150	75	40
	80		230	150	180	110	22	100	35	145		16		190	90	55

⑨型式の最後にMWコードをご指定いただいた場合、ノックピン落下防止用ワッシャ (P-1145) を付属し出荷いたします (MGHPの在庫品・MTO(受注製作品)ともに適用)。MWご指定による出荷日の変更はございません。該当するMWは追加工欄をご参照ください。



●ボス外径に鋳物肌が残る場合がありますが、機能上問題ありません。

④在庫品型式にMWご指定の場合は在庫品の納期、MTO(受注製作品)にMWご指定の場合はMTO(受注製作品)の納期にて出荷(MGHP)いたします。