



先端加工付ブロックコアピン



RoHS 10



フランジ部の逃し




Type	材質	硬度	公差 J・E・A・V
BCSH	SKH51	61~64HRC	±0.005
BCSR	RIGOR®	53~55HRC	
BCSA	ORVAR® SUPREME	51~53HRC	
BCSV		47~49HRC	
BCSN	NAK80	37~43HRC	

ORVAR® SUPREME および RIGOR® はウッデホルム株式会社の登録商標です。


ブロックコアピン精度基準詳細 P.469

■フランジ位置




F0 F90 F180 F270


1A




2A




3A




4A




5A




6A




7A




8A




9A




10A




11A




12A



1B



2B



E寸精度はE±0.02となります。 E < W

E・J寸精度はE±0.02 J±0.02となります。 E ≤ J < W

型式		指定0.01mm単位							H	F	ℓ max.
Type	Shape	L	P	W	N	J・E・A・V	Emin.	Vmin.			
BCSH (SKH51)	1A 7A	20.00	1.00~1.99	1.00~10.00	N > L/2	P > E P > J ≥ E W > V W > A ≥ V	0.5	0.5	4	0	ℓ ≤ E × 5
BCSR (RIGOR®)	2A 8A		2.00~3.00	1.00~15.00			1.00	ℓ and			
BCSA	3A 9A		3.01~5.00	1.00~20.00			1.50	ℓ ≤ V × 5			
BCSV (ORVAR® SUPREME)	4A 10A		5.01~10.00	2.00~20.00			2.50	ℓ and			
BCSN (NAK80)	5A 11A		10.01~15.00	2.00~20.00			5.00	ℓ ≤ 5			
	6A 12A		15.01~20.00	3.01~20.00			7.50	(P < 2 or W < 2)			

ORVAR® SUPREME および RIGOR® はウッデホルム株式会社の登録商標です。
 * P < 2.00 → L ≤ 50.00 W < 2.00 → L ≤ 50.00 BCSRは、W ≤ 3.49 → L ≤ 50.00

Order 注文例: 型式 [L][P][W][N][J][E][A][V][H][F] BCSR12A - 36.50 - P4.39 - W5.61 - N31.5 - J3.80 - E2.80 - A4.50 - V4.20 - H6 - F0 BCSH5A - 50.00 - P5.05 - W6.00 - N30.0 - A5.25 - V5.25 - H6 - F90

Delivery 出荷日: 5 日日出荷

Alterations 追加加工: 型式 [L][P][W][N][J][E][A][V][H][F] (CGC・RGC・TC) BCSR12A - 36.50 - P4.39 - W5.61 - N31.5 - J3.80 - E2.80 - A4.50 - V4.20 - H6 - F0 - TC0.5

追加工	記号	詳細
CGC	CGC	通常R ≤ 0.1の形状継ぎ目部分を指定可能なC面に変更します。(45°) CGC = 指定0.1mm単位 0.1 ≤ CGC ≤ 5.0 and CGC < ℓ 先端形状別 加工限界
RGC	RGC	通常R ≤ 0.1の形状継ぎ目部分のRを指定できます。 RGC = 指定0.1mm単位 0.1 ≤ RGC ≤ 5.0 and RGC < ℓ 先端形状別 加工限界
TC	TC	フランジ幅変更(フランジ幅0.3~3.0の間で変更できます。) TC = 指定0.1mm単位 L20.00~30.00 → 0.3 ≤ TC ≤ 1.5 L30.01~50.00 → 0.3 ≤ TC ≤ 2.5 L50.01~70.00 → 0.3 ≤ TC ≤ 3.0

規格対応表

型式	記号	規格							
		L	20.00 ~ 70.00	20.00 ~ 50.00	規格無し				
Type	Shape	W	P	1.00~1.99	2.00~3.00	3.01~5.00	5.01~10.00	10.01~15.00	15.01~20.00
BCSH		1.00~1.99	△	△	△	△	△	△	△
BCSR		2.00~3.00	△	△	△	△	△	△	△
BCSA	1A 7A	3.01~5.00	△	△	△	△	△	△	△
BCSV	2A 8A	5.01~10.00	△	△	△	△	△	△	△
BCSN	3A 9A	10.01~15.00	△	△	△	△	△	△	△
	4A 10A	15.01~20.00	△	△	△	△	△	△	△
	5A 11A	1.00~1.99	△	△	△	△	△	△	△
	6A 12A	2.00~3.49	△	△	△	△	△	△	△
	1B 2B	3.50~5.00	△	△	△	△	△	△	△
		5.01~10.00	△	△	△	△	△	△	△
		10.01~15.00	△	△	△	△	△	△	△
		15.01~20.00	△	△	△	△	△	△	△

ブロックコアピン