


CUSHION PINS クッションピン



M×P	S	B	C	型式		L 指定10mm単位
				Type	D	
10×1.5	15	8	5	RCUP	16	50~200
12×1.75	18	10	6		20	50~250
16×2.0	24	14	9		25	50~250
20×2.5	30	17	12		32	50~250


RCUPのおねじ径は、MCUPより1ランク大きくなっています。

Order 注文例: 型式 - L
RCUP 20 - 200

Delivery 出荷日: 3 日日出荷

Alterations 追加加工: 型式 - L(LC) - (LKC)
RCUP 20 - LC195 - LKC

追加加工	記号	詳細
	LC	全長変更 35 ≤ LC < L 指定1mm単位
	LKC	全長公差変更 L公差 $0 \rightarrow -0.04$ LC併用のとき、LCを0.1mm単位で指定可




M×P	S	B	F	型式		L 指定10mm単位
				Type	D	
8×1.25	12	13	16	MCUP	16	50~250
10×1.5	15	16			20	50~250
12×1.75	18	18			25	50~250
16×2.0	24	21			32	100~250

Order 注文例: 型式 - L
MCUP 20 - 200

Delivery 出荷日: 3 日日出荷

Alterations 追加加工: 型式 - L(LC) - (LKC・MC)
MCUP 20 - LC195 - LKC

追加加工	記号	詳細												
	LC	全長変更 35 ≤ LC < L 指定1mm単位												
	LKC	全長公差変更 L公差 $0 \rightarrow -0.04$ LC併用のとき、LCを0.1mm単位で指定可												
	MC	タップ加工 <table border="1"> <thead> <tr> <th>D</th> <th>M</th> <th>ℓ</th> </tr> </thead> <tbody> <tr> <td>16</td> <td>8</td> <td rowspan="4">2×M</td> </tr> <tr> <td>20</td> <td>10</td> </tr> <tr> <td>25</td> <td>12</td> </tr> <tr> <td>32</td> <td>16</td> </tr> </tbody> </table>	D	M	ℓ	16	8	2×M	20	10	25	12	32	16
D	M	ℓ												
16	8	2×M												
20	10													
25	12													
32	16													



H	型式		L 指定10mm単位
	Type	D	
15	HCUP	10	50~200
18		13	50~250
21		16	50~250
25		20	50~250
30		25	50~250
37		32	50~250

Order 注文例: 型式 - L
HCUP 13 - 150

Delivery 出荷日: 3 日日出荷

Alterations 追加加工: 型式 - L(LC) - (LKC・MC・NC)
HCUP 13 - LC155 - LKC

追加加工	記号	詳細												
	LC	全長変更 35 ≤ LC < L 指定1mm単位												
	LKC	全長公差変更 L公差 $0 \rightarrow -0.04$ LC併用のとき、LCを0.1mm単位で指定可												
	MC	タップ加工 <table border="1"> <thead> <tr> <th>D</th> <th>M</th> <th>ℓ</th> </tr> </thead> <tbody> <tr> <td>10</td> <td>8</td> <td rowspan="4">2×M</td> </tr> <tr> <td>13-16</td> <td>8</td> </tr> <tr> <td>20</td> <td>10</td> </tr> <tr> <td>25-32</td> <td>12</td> </tr> </tbody> </table>	D	M	ℓ	10	8	2×M	13-16	8	20	10	25-32	12
D	M	ℓ												
10	8	2×M												
13-16	8													
20	10													
25-32	12													
	NC	タップ加工 <table border="1"> <thead> <tr> <th>D</th> <th>M</th> <th>ℓ</th> </tr> </thead> <tbody> <tr> <td>10</td> <td>6</td> <td rowspan="4">2×M</td> </tr> <tr> <td>13-16</td> <td>8</td> </tr> <tr> <td>20</td> <td>10</td> </tr> <tr> <td>25-32</td> <td>12</td> </tr> </tbody> </table>	D	M	ℓ	10	6	2×M	13-16	8	20	10	25-32	12
D	M	ℓ												
10	6	2×M												
13-16	8													
20	10													
25-32	12													

自動車用
小物部品