

# 全長ショート曲げ・面打ちパンチ&ダイ

ー外形固定タイプー

¥追加工価格も数量スライド適用 [P.43](#)

Type (先端形状は下図より選択)								
BPHMS (タップ付)		BPHFS (片フランジ)		BPHWS (両フランジ)				
				フランジ部詳細 				
<b>H</b>	<b>l</b>	<b>l</b>	<b>l</b>	<b>M</b> 材質 SKD11相当				
6	6	8.5						
8	7.5	10						
10	9	12.5						
13								
16	12	15.5						
20								
先端形状								
<b>2A</b>	<b>J</b>	<b>3B</b>	<b>J</b>	<b>4B</b>	<b>K</b>	<b>2C</b>	<b>J</b>	
<b>F=L</b>		<b>F</b>	<b>A</b>	<b>F</b>	<b>S</b>	<b>F=L-S</b>	<b>N</b>	
					<b>C</b>	<b>S</b>	<b>Q</b>	
					<b>0.01</b>	<b>0.02</b>	<b>0.01</b>	
<b>3C</b>	<b>J</b>	<b>4C</b>	<b>J</b>	<b>2D</b>	<b>R0.5</b>	<b>3D</b>	<b>J</b>	
<b>F</b>		<b>F=L-S</b>	<b>S</b>	<b>F</b>	<b>R0.5</b>	<b>F</b>	<b>N</b>	
					<b>0.5</b>	<b>0.02</b>	<b>0.01</b>	
<b>4D</b>	<b>J</b>	指定単位 C-J-K-N-Q-S-U--->0.01mm単位 B-E----->0.1mm単位 A-G----->0.5°単位		加工限度 J-K=0 or J-K-Q≥0.2 N-U≥0.2 1≤B≤14.5 U≤C 0.2≤C≤V-2 K+N≤S≤14.5 K+U≤S≤14.5				
型式		<b>V</b>	<b>6</b>	<b>8</b>	<b>10</b>	<b>13</b>	<b>16</b>	<b>20</b>
Type	Shape形状							
タップ付	BPHMS	2A 3B	6	○	○	○	○	○
		4B 2C	8	○	△	△	△	△
片フランジ	BPHFS	3C 4C	10	○	△	□	□	□
		2D 3D	13	○	△	□	●	●
両フランジ	BPHWS	4D	16	○	△	□	●	●
			20	○	△	□	●	●

○表中の印とタップM×lの関係

○: M4×6 □: M6×9  
△: M5×7.5 ●: M8×12

Order 注文例 タップ付 型式 **V** **H** - **L** - **B-C-E-J-K-N-Q-S-U-A-G**  
BPHMS 3B 06 06 - 24.5 - C2.00 - J1.50 - K2.00 - A60

フランジ付 ■フランジ位置指定(無料)



型式 **V** **H** - **L** - **B-C-E-J-K-N-Q-S-U-A-G** - **F-WF**  
BPHFS 3B 08 16 - 20.0 - C2.00 - J1.50 - K2.00 - A60 - F0  
BPHWS 3D 16 13 - 25.0 - C6.00 - J0.50 - K0.50 - N1.30 - Q0.50 - S14.50 - WF90

Delivery 出荷日 **5** 日目出荷

Alterations 追加工

型式 **V** **H** - **L** - **B-C-E-J-K-N-Q-S-U-A-G** - **F-WF** - (HC・TC・etc.)  
BPHFS 2A 06 06 - 20.0 - J1.00 - K2.00 - F0 - HC1.3 - TKC

Alterations	Code	Spec.	¥/1Code
	HC	フランジ幅変更 0≤HC<1.5 指定0.1mm単位	200
	TC	フランジ厚変更 2≤TC<5 指定0.1mm単位	200
	TKC	フランジ厚公差変更 5+0.2 -0.02 → 0.02	200

Alterations	Code	Spec.	¥/1Code																																								
	LKC	全長公差変更 +0.2 -0.02 → +0.02 適用不可	800																																								
	MC	タップ径変更 <table border="1"><tr><td>H</td><td>V</td><td>6</td><td>8</td><td>10</td><td>13</td><td>16</td><td>20</td></tr><tr><td>6</td><td>-</td><td>M4</td><td>M3</td><td></td><td></td><td></td><td></td></tr><tr><td>8</td><td>-</td><td></td><td>M5</td><td>M4</td><td></td><td></td><td></td></tr><tr><td>10</td><td>-</td><td></td><td></td><td>M6</td><td>M5</td><td></td><td></td></tr><tr><td>13</td><td>-</td><td></td><td></td><td></td><td>M8</td><td>M6</td><td></td></tr></table>	H	V	6	8	10	13	16	20	6	-	M4	M3					8	-		M5	M4				10	-			M6	M5			13	-				M8	M6		0
H	V	6	8	10	13	16	20																																				
6	-	M4	M3																																								
8	-		M5	M4																																							
10	-			M6	M5																																						
13	-				M8	M6																																					

Price 価格

数量スライド価格 (1円未満切り捨て) [P.39](#)

数量区分	標準対応	個別対応 大口
数量	1~9	10~29
基準単価	5%	10%
値引率	10%	15%
	お見積り	

表示数量超えはWOSにてご確認ください。


■H≤Vの場合

Type	H	形状	¥基準単価 1~9本			
			<b>A</b>	<b>B</b>	<b>C</b>	<b>D</b>
BPHMS	6	3,770	4,070	7,520	8,390	
	8・10	4,140	4,470	8,280	9,240	
	13・16	4,890	5,270	9,360	10,450	
	20	5,380	5,800	10,300	11,500	
BPHFS	6	3,990	4,320	8,130	9,080	
	8・10	4,390	4,770	8,950	10,000	
	13・16	5,210	5,640	10,140	11,340	
	20	5,750	6,220	11,170	12,480	
BPHWS	6	4,140	4,470	8,280	9,240	
	8・10	4,550	4,930	9,110	10,160	
	13・16	5,360	5,800	10,300	11,500	
	20	5,910	6,380	11,330	12,640	

Type	H	形状	¥基準単価 1~9本			
			<b>A</b>	<b>B</b>	<b>C</b>	<b>D</b>
BPHMS	6	-	-	-	-	-
	8・10	5,390	5,830	10,780	12,020	
	13・16	6,380	6,860	12,170	13,590	
	20	7,000	7,550	13,390	14,970	
BPHFS	6	-	-	-	-	-
	8・10	5,720	6,200	11,660	13,010	
	13・16	6,780	7,350	13,190	14,760	
	20	7,490	8,090	14,530	16,230	
BPHWS	6	-	-	-	-	-
	8・10	5,920	6,410	11,860	15,420	
	13・16	6,990	7,550	13,390	17,420	
	20	7,690	8,300	14,730	19,170	


Example 使用例

■特長 タップ長・下穴を短くおさえることで先端加工の寸法限度を広げることが可能になりました。



面打ち

上曲げ



ストリッパプレート

ダイプレート