


d ₁	d ₂	型式		指定10mm単位	
		Type	D	L	S
33	33	STB	20		
45	44	STB-N	32	100~300	0~150
33	33	STBY	20		
45	44	STBY-N	32		



※S=10のときのみA=20(D20)、A=32(D32)となります。

型式 - L - S
STB 20 - 100 - 100
STB-N 32 - 40
3 日目出荷 急 ストク A




e	d ₁	d ₂	型式		指定10mm単位	
			Type	D	L	S
26.0	21	30	MRTB	20		
37.5	32	40	MRTB-N	30	100~300	0~150
26.0	21	30	MRTBY	20		
37.5	32	40	MRTBY-N	30		


型式 - L - S
MRTB 20 - 100 - 100
MRTB-N 30 - 40
3 日目出荷 急 ストク A



RoHS10



RoHS10



E	F	D ₁	型式	
			Type	D
40	15	32	SCTB	20
45	20	46	SCTBY	30

Order
注文例
型式
SCTB 30

Delivery
出荷日
3 日目出荷
ストク A

Alterations
追加工
型式
SCTB 20 - LC100

追加工
記号
LC
詳細
L寸法をカットします。
80≤LC≤235
指定5mm単位