


PRESS

CAM STROKE PLATES -30° TYPE-




カムストロークプレート

-30° タイプ-

新商品
赤文字表示

RoHS

CS30W(銅合金タイプ)

CS30F(スチールタイプ)
CS30FN(スチールタイプ 油溝無し)■材質 銅合金
特殊固体潤滑剤(埋設)

■材質 SUS304

■カムストロークプレート用シム

c	l	a	b	型式	呼び(カムストロークプレート)	板厚
				SPCSP	W	L
65	120	40	50	SPCSP	75	130
			45		150	130
90	120	60	50		100	130
			45		150	130
115	120	85	50		125	130
			45		150	130
140	120	110	50		150	130
			45		150	150

(注) l=130、150に限る

型式 W - L - T
CS30W 100 - 200 - 0.1
SPCSP 75 - 130 - 0.1

出荷日




価格



使用例

お見積り、ご注文方法

WOS(Web Order System):
<http://ec.misumi.jp/> P.46
TEL: 0120(343)066
FAX: 0570(034)355 P.1607

T	l	a	b	型式	W	L
30	95		50	CS30W	130	
45	90	40	45		150	
60	120		75		170	
30	95		50		200	
45	90	60	45	CS30F	130	
60	120		75		150	
30	95		50		170	
45	90	85	45		200	
60	120		75	CS30FN	130	
30	95		50		150	
45	90	110	45		170	
60	120		75		200	

PRESS

CAM STROKE PLATES -15° TYPE-






カムストロークプレート

-15° タイプ-

新商品
赤文字表示

RoHS

CS15W(銅合金タイプ)

CS15F(スチールタイプ)
CS15FN(スチールタイプ 油溝無し)■材質 銅合金
特殊固体潤滑剤(埋設)

T	a	型式	W	L
25		CS15W	110	
30			130	
35			150	
25	40	CS15F	110	
30			130	
35			150	
25	60	CS15FN	110	
30			130	
35			150	

Delivery 出荷日
Order 型式 W - L
CS15W 50 - 110


お見積り、ご注文方法

WOS(Web Order System):
<http://ec.misumi.jp/> P.46TEL: 0120(343)066
FAX: 0570(034)355 P.1607

価格



使用例



カム・関連部品