










詳細 P.63





ディコート®処理

P.1729

シャング径 D公差		材質 硬度		型式		刃先形状は下記A D R E Gより選択	
				Type	刃先形状	刃先長さ B	ノック穴付
D _{m5}		SKD11相当 60～63HRC 表面3000HV		T-SP	A D R E G	S L X 刃先長さ (B) X>L>S	-C
RoHS 10							
							
							
A付属品 MS6-25							

刃先形状		刃先形状		刃先形状		刃先形状		刃先形状	
A		D		R		E		G	
									
		⊙ P≥W ⊙ K=√P²+W² ⊙ R=0の指定可		⊙ P≥W ⊙ K=√(P-2R)²+(W-2R)²+2R ⊙ 0.15≤R<W/2		⊙ P>W		⊙ P>W	

		型式														指定0.01mm単位				B	H		
Type	刃先形状	B 刃先長さ	ノック穴付	D	L												A		D R E G			R(D)	
																	min. P max.		P・Kmax. P・Wmin.			R	
T-SP	<div><div>A</div><div>D</div><div>R</div><div>E</div><div>G</div></div>	<div>S</div> <div></div>	-C	<div><div>0.15</div><div>∩</div><div>W/2</div><div>未満</div><div>(D 0のみ指定可)</div></div>	10	(40)	50	60	70	80	90	100					3.00~	9.99	9.97	2.50	13	13	
					13	(40)	50	60	70	80	90	100					6.00~	12.99	12.97	3.00		16	
					16	(40)	50	60	70	80	90	100					10.00~	15.99	15.97	4.00		19	
					20	(40)	50	60	70	80	90	100					13.00~	19.99	19.97	5.00		23	
					25	(40)	50	60	70	80	90	100					18.00~	24.99	24.97	6.00		28	
					32	(40)	(50)	60	70	80	90	100	110	120			20.00~	31.99	31.97	7.00		35	
					38	(40)	(50)	60	70	80	90	100	110	120			28.00~	37.99	37.97	8.00		41	
					45	(40)	(50)	60	70	80	90	100	110	120			35.00~	44.99	44.97	9.00		48	
		10				50	60	70	80	90	100					3.00~	9.99	9.97	2.50	19	13		
		13				50	60	70	80	90	100					6.00~	12.99	12.97	3.00		16		
		16				60	70	80	90	100					10.00~	15.99	15.97	4.00	19				
		20				60	70	80	90	100					13.00~	19.99	19.97	5.00	23				
		25				60	70	80	90	100					18.00~	24.99	24.97	6.00	28				
		32				60	70	80	90	100	110	120			20.00~	31.99	31.97	7.00	35				
		38				60	70	80	90	100	110	120			28.00~	37.99	37.97	8.00	41				
		45				60	70	80	90	100	110	120			35.00~	44.99	44.97	9.00	48				
		10					70	80	90	100					6.00~	9.99	—		—	30	13		
		13					70	80	90	100					6.00~	12.99					16		
		16					80	90	100					10.00~	15.99	19							
		20					80	90	100					13.00~	19.99	23							
		25					80	90	100					18.00~	24.99	28							
		32					80	90	100	110	120			20.00~	31.99	35							
		38					80	90	100	110	120			28.00~	37.99	41							
		45					80	90	100	110	120			35.00~	44.99	48							
	<div>X</div> <div></div>																	40	13				
																			16				
																			19				
																			23				
																			28				
																			35				
																			41				
																			48				