


■文字付き


高硬度タイプ
PINH

■文字無し

型式 Type		L 指定0.1mm単位	Order 注文例	型式 - L - CHR PIN 10 - 60.5 - 53218A PINH-N8 - 156.2	
	D				
	3*				
	4*				
	5				
	6				
PIN-N (D3 ~ 30)	7			Delivery 出荷日	
	8				3 日旨出荷
	9				ストック A
高硬度タイプ PINH-N (D5~30)	10	10.0~250.0		Alterations 追加工	
	11				
	12				
	13				
	14				
	15				
	16				
	18				
	20				
	22				
	25				
	27				
	30				




 Order 注文例	型式 MSK 50	 Delivery 出荷日	 在庫品
--	--------------	---	---



型式		L 指定1mm単位
Type	D	
PRPS (L≥40)	8	20 ~ 150
	10	
	13	
	16	
	20	
	25	
PRP	28	20 ~ 200



■落下防止用止め金



■ プレッシャーピン専用カラー

