


インローメネジ止めタイプ

RoHS10

SKSTH (P寸・B寸指定)



●ニゲ溝詳細

M 材質 SKS3
H 硬度 60 ~ 63HRC

| D _{m6} | | M | L | (S) | 型式 Type | D | P 指定0.01mm単位 | B 指定0.1mm単位 |
|-----------------|--------|---|----|-----|------------|----|-----------------|----------------|
| 5 | -0.004 | 3 | 12 | 8 | SKSTH | 5 | 8.00~8.99 | 1.0~12.0 |
| | -0.012 | | | 10 | | 6 | 9.00~10.00 | |
| | | | | 12 | | 6 | 10.00~10.99 | |
| | -0.005 | 4 | 15 | 15 | | 8 | 11.00~12.00 | |
| | -0.014 | | | 17 | | 8 | 12.00~12.99 | |
| | | | | 20 | | 10 | 13.00~16.00 | |
| | -0.006 | 6 | 20 | 10 | | 10 | 14.00~14.99 | |
| | -0.017 | | | 13 | | 13 | 15.00~20.00 | |
| | | | | 25 | | 16 | 16.00~16.99 | |
| | | | | 24 | | | 17.00~20.00 | |
| | | | | 25 | | | 18.00~20.00 | |


Order
注文例
SKSTH 8 - P12.80 - B3.5

Delivery
出荷日
3 日目出荷
ストーク A


圧入タイプ

RoHS10

SFSTH (P寸・B寸指定)



※ (S) ≈ 1.6 × P となります。

M 材質 SKS3
H 硬度 60 ~ 63HRC

| D _{m6} | | L | 型式 Type | D | P 指定0.01mm単位 | B 指定0.1mm単位 | |
|-----------------|--------|----|------------|----|-----------------|----------------|--|
| 4 | +0.012 | 12 | SFSTH | 4 | 4.00~8.00 | 1.0~12.0 | |
| | +0.004 | | | 5 | 5.00~10.00 | | |
| | | | | 6 | 6.00~12.00 | | |
| | +0.015 | 15 | | 8 | 8.00~14.00 | | |
| | +0.006 | | | 10 | 10.00~16.00 | | |
| | +0.018 | 20 | | 13 | 13.00~18.00 | | |
| | +0.007 | | | 16 | 16.00~20.00 | | |
| | | | | | | | |
| | | | | | | | |
| | | | | | | | |


Order
注文例
SFSTH 6 - P7.98 - B4.5

Delivery
出荷日
3 日目出荷
ストーク A



Example

使用例




LOCATING PILOT PINS

位置決めパイロットピン


RoHS10

PST

M 材質 SKS3
H 硬度 60 ~ 63HRC

RoHS10

PSTM

M 材質 SKS3
H 硬度 60 ~ 63HRC

| B | S | 型式 Type | D | L | P 指定0.01mm単位 |
|---|----|------------|----|----|-----------------|
| 1 | 4 | PST | 1 | 12 | 1.50~3.00 |
| | 5 | | 2 | 12 | 2.50~4.00 |
| | 6 | | 3 | 12 | 4.00~6.00 |
| | 7 | | 4 | 15 | 5.00~7.00 |
| | 8 | | 5 | 15 | 6.00~8.00 |
| | 9 | | 6 | 15 | 7.00~9.00 |
| | 10 | | 8 | 15 | 9.00~13.00 |
| | 18 | | 10 | 18 | 11.00~15.00 |
| | | | | | |
| | | | | | |

Order
注文例
PSTM 5 - 15 - P7.20

Delivery
出荷日
3 日目出荷
ストーク T
ストーク A

Alterations
追加工
PSTM 5 - 15 - P7.20 - BC3.5

| 追加工 | 記号 | 詳細 |
|-----|----|--|
| PC | | 先端径変更 PC: Pmin=0.2 指定0.01mm単位 |
| BC | | B寸変更 1≤BC≤Bmax 指定0.1mm単位 ※S寸法は変わりません。 |
| PKC | | 先端径 P: +0.01 → +0.005 |

