


# PLATES FOR GAS SPRINGS ガススプリング用プレート -上溝固定タイプ-

**RoHS10**



**FCC**      **FC19-25**




材 質 S45C相当  
表面処理 四三酸化鉄皮膜 (Fe<sub>3</sub>O<sub>4</sub>)

---

**RoHS10**



**FC32・38・45・50・63・75・95・120・150**  
**FCB**



材 質 S45C相当  
表面処理 四三酸化鉄皮膜 (Fe<sub>3</sub>O<sub>4</sub>)

A	a	B	d	t	h			型式	適用ガススプリング						推奨ボルト 2本	
					GSV	GSSC	GSU		GSV	GST	GSH	GSK	GSSC	GSU		
34	24	21	6.6	9	-	-	21.5	FCC	12	-	-	-	-	-	50	CB6-18
37	27	24	6.6	9	-	-	21.5		15	-	-	-	-	-	70	CB6-18
44	32	25	6.6	9	21.5	-	21.5		19	170	-	-	-	-	90	CB6-18
50	38	30	6.6	9	21.5	18	21.5		25	320	-	-	-	400	200	CB6-18


A	a	B	b	d	t	h				型式	適用ガススプリング						推奨ボルト 4本	
						GSV	GST	GSH	GSK		GSV	GST	GSH	GSK	GSSC	GSU		
44	30	25	12	6.6	9	21.5	-	-	21.5	FC	19	170	-	-	-	90	CB6-18	
50	34	30	18	6.6	9	21.5	-	18	21.5		25	320	-	-	400	200	CB6-18	
60	-	35	-	7	9	17	-	16	15		32	350	350	-	150	750	300	CB6-18
68	-	40	-	7	9	17	-	15	-		38	500	500	-	250	1000	-	CB6-18
86	-	50	-	9	13	23	-	-	-		45	750	750	-	500	-	-	CB8-25
95	-	56.5	-	9	13	24	22	-	-		50	1000	1000 1200	1000	750	-	-	CB8-25
122	-	73.5	-	11	16	27	27	-	-		63	1500	1500	1500	-	-	-	CB10-35
122	-	73.5	-	11	16	29	29	-	-		75	2400	2400	2400	1500	-	-	CB10-35
150	-	92	-	13.5	18	33	33	-	-		95	4200	4200	4200	3000	-	-	CB12-40
175	-	109.5	-	13.5	21	36	36	33	-		120	6600	6600	6600	5000	12000	-	CB12-40
220	-	138	-	17.5	27	41	-	38	-		150	9500 12000	9500	-	-	18500	-	CB16-55

A	B	d	t	h	型式	適用ガススプリング GSSC		推奨ボルト 4本
95	56.5	9.0	13	21	FCB	50	1800	CB8-30
122	73.5	11.0	16	27		63	3000	CB10-35
122	73.5	11.0	16	26		75	4700	CB10-35
150	92.0	13.5	18	30		95	7500	CB12-40

**RoHS10**



**FCQ**  
**FCQB**



材 質 S45C相当  
表面処理 四三酸化鉄皮膜 (Fe<sub>3</sub>O<sub>4</sub>)

A	a	d	g	型式	適用ガススプリング						推奨ボルト 4本	
					GSV	GST	GSH	GSK	GSSC	GSU		
45	35	6.6	9	FCQ	32	350	350	-	150	750	300	CB 6-18
52	40	6.6	9		38	500	500	-	250	1000	-	CB 6-18
64	50	9	13		45	750	750	-	500	-	-	CB 8-25
70	56.5	9	13		50	1000	1000 2000	1000	750	-	-	CB 8-25
90	73.5	11	16		63	1500	1500	1500	-	-	-	CB10-35
90	73.5	11	16		75	2400	2400	2400	1500	-	-	CB10-35
110	92	13.5	18		95	4200	4200	4200	3000	-	-	CB12-40
130	109.5	13.5	21		120	6600	6600	6600	5000	12000	-	CB12-40
162	138	17.5	27		150	9500 12000	9500	-	-	18500	-	CB16-55
210	170	17.5	27		195	20000	-	-	10000	-	-	CB16-55

A	a	d	g	型式	適用ガススプリング						推奨ボルト 4本	
					GSV	GST	GSH	GSK	GSSC	GSU		
70	56.5	9	13	FCQB	50	-	-	-	-	1800	-	CB 8-25
90	73.5	11	16		63	-	-	-	-	3000	-	CB10-35
90	73.5	11	16		75	-	-	-	-	4700	-	CB10-35
110	92	13.5	18		95	-	-	-	-	7500	-	CB12-40

■上溝固定タイプのプレートは荷重をプレートで受ける事が可能です。  
但し、荷重は取付部全面で受けてください。

Order  
注文例

型式

**FC12**  
**FC38**  
**FCB63**  
**FCQ50**  
**FCQB63**

Delivery  
出荷日

**MiSUMI-VONA** にてお見積りください。  
(<http://ec.misumi.jp>)