





H	T	型式			L 指定10mm単位
		Type	先端加工	D	
18	8	POP HPOP (高周波焼入タイプ)	N R U	8	30~120
25				10	40~150
28				13	50~180
30				16	50~180
35				20	50~200
40				25	50~200

Order
注文例

Type	型式
POP	R 16
	- L

Delivery
出荷日

3	日目出荷
急	ストーク A



型式		L
Type	D	
DHPA	20	120
		170
		220
		260

Order
注文例

Type	型式	- L
DHPA 20	- 120	

Delivery
出荷日

在庫品
