


a	b	L1	型式	W	L
15	30	114	CKF	60	171
		134			191
20	40	114		80	171
		124			191

a	b	c	d	d1	e	T	型式	W	L
15	30	11	11	17.5	18	30	CKB CKBK	25	60
20	40	16	13	20	23	38		32	60 80







型式 (W) (L)



KMKW	48	60
KMKS		
KMKK		

$\ell$	型式	(W)	L
52.5			100
72.5	CKFU	60	120



40		20		CKFX	80		
$\ell_1$	T	t	d	ボルト 穴数	型式	W	L
							5

7.5	16	8	10	1	CKFC	30	5
10	18	10	12	2		50	7
<i>ℓ</i>		型式		W	L		
32.4		CKFC		30	67.5		

