


## ミスミ

SOLID CARBIDE DRILLS

## 超硬ドリル

●ストレートシャンク／スタブ -STRAIGHT SHANK／STUB LENGTH-

## C-SDB



材質	超硬			直徑D、シャンク径d	公差(h7)				
仕様	先端角 118° スタブ 22°~27° 再研磨			0.5~3	0 -0.010				
				3.1~6	0 -0.012				
				6.1~8	0 -0.015				
一般鋼 (SS-SC材)	合金鋼 (SCM)	調質鋼 (~45HRC)	高硬度鋼 (50HRC~)	工具鋼 (SKD, SKS)	ステンレス鋼 (SUS)	鋳鉄 (FC, FCD)	アルミ (Al)	銅 (Cu)	樹脂
○	○			○		○	○	○	

○=適

## 型番 C-SDB 1本単位

直徑 D	溝長 l	全長 L	¥通常単価 30本以上はお見積り		
			1~4本	5~9本	10~29本
0.5	3	20	1,130	1,000	980
0.6	3.5	21	1,130	1,000	980
0.7	4.5	23	1,130	1,000	980
0.8	5	24	1,130	1,000	980
0.9	5.5	25	1,130	1,000	980
1	6	26	900	800	780
1.1	7	28	900	800	780
1.2	8	30	960	840	830
1.3	8	30	960	840	830
1.4	9	32	1,020	900	880
1.5	9	32	1,020	900	880
1.6	10	34	1,070	940	920
1.7	10	34	1,070	940	920
1.8	11	36	1,070	940	920
1.9	11	36	1,070	940	920
2	12	38	1,280	1,130	1,100
2.1	12	38	1,290	1,130	1,110
2.2	13	40	1,290	1,130	1,110
2.3	13	40	1,290	1,130	1,110
2.4	14	43	1,430	1,260	1,240
2.5	14	43	1,430	1,260	1,240
2.6	14	43	1,430	1,260	1,240
2.7	16	46	1,730	1,520	1,490
2.8	16	46	1,730	1,520	1,490
2.9	16	46	1,750	1,540	1,510
3	16	46	1,740	1,530	1,500
3.1	18	49	1,820	1,680	1,640
3.2	18	49	1,930	1,780	1,750
3.3	18	49	1,930	1,780	1,750
3.4	20	52	2,180	2,020	1,980

直徑 D	溝長 l	全長 L	¥通常単価 30本以上はお見積り		
			1~4本	5~9本	10~29本
3.5	20	52	2,120	1,960	1,920
3.7	20	52	2,300	2,120	2,080
3.9	22	55	2,450	2,260	2,210
4	22	55	2,550	2,360	2,310
4.1	22	55	2,650	2,440	2,390
4.2	22	55	2,650	2,440	2,390
4.3	24	58	2,930	2,710	2,650
4.4	24	58	2,930	2,710	2,650
4.5	24	58	2,860	2,640	2,580
4.6	24	58	2,930	2,710	2,650
4.9	26	62	3,140	2,900	2,840
5	26	62	3,080	2,840	2,780
5.1	26	62	3,210	2,970	2,910
5.3	26	62	4,140	3,820	3,740
5.4	28	66	4,280	3,960	3,880
5.5	28	66	4,280	3,960	3,880
5.7	28	66	4,640	4,290	4,200
5.8	28	66	4,640	4,290	4,200
5.9	28	66	4,710	4,360	4,270
6	28	66	4,640	4,290	4,200
6.1	31	70	5,860	5,410	5,300
6.2	31	70	5,860	5,410	5,300
6.5	31	70	5,430	5,010	4,910
6.6	31	70	6,860	6,330	6,200
6.7	31	70	6,860	6,330	6,200
6.8	34	74	6,860	6,330	6,200
7	34	74	6,140	5,670	5,560
7.5	34	74	7,080	6,540	6,400
8	37	79	7,570	6,990	6,850

切削条件 P.644

Order  
注文例C-SDB 5  
型番 直径(D)Delivery  
出荷日

在庫品

卷末-7

ご希望によりPM6:00迄、当日出荷受付致します。

が特長!

汎用の超硬ドリルで幅広い用途に対応できます。

