



COMPONENTS FOR LIFTING AND DIE STORING 吊り具・型保管部品



LIFTING BARS リフティングバー



D ₁	L	l	許容荷重 4本使用時 N{kgf}	型式	Type	D
34	185	135	29420 [3000]	HLFB	25	
44	240	190	49033 [5000]		35	
50	260	210	88260 [9000]		40	
60	290	240	137293 [14000]		50	
75	335	285	166712 [17000]		65	

*荷重 (kgf) = 荷重N×0.101972



②抜け止めのストッパーが必ず下に出る様にセットしてご使用ください。
ツバ部が型からはみ出さない様にセットしてご使用ください。

