


ハイス鋼ドリル

● テーパーシャンク / レギュラー -TAPER SHANK / REGULAR LENGTH-

YTD



材質	HSS	ホモ 処理
----	-----	----------



直徑D	公差(h8)
13.5~18	0 -0.027
18.5~30	0 -0.033

一般鋼 (SS-SC材)	合金鋼 (SCM)	調質鋼 (~45HRC)	高硬度鋼 (50HRC~)	工具鋼 (SKD, SKS)	ステンレス鋼 (SUS)	鋳鉄 (FC, FCD)	アルミ (Al)	銅 (Cu)
○								

○=適

型番 YTD 1本単位

直徑 D	溝長 l	全長 L	MT No.	¥通常単価 20本以上お見積り		
				1本	2~9本	5~19本
13.5	108	189	1	1,560	1,520	1,480
14	108	189	1	1,610	1,570	1,530
16	120	218	2	2,030	1,960	1,930
16.5	125	223	2	2,220	2,150	2,110
17	125	223	2	2,330	2,260	2,210
18	130	228	2	2,570	2,490	2,440
18.5	135	233	2	2,640	2,560	2,510
19	135	233	2	2,770	2,680	2,630
20	140	238	2	2,910	2,820	2,770
20.5	145	243	2	2,950	2,860	2,810
21	145	243	2	3,070	2,980	2,920
22	150	248	2	3,280	3,180	3,110
22.5	155	253	2	3,430	3,330	3,250
23	155	253	2	3,560	3,450	3,380
23.5	155	276	3	3,870	3,750	3,670
24	160	281	3	4,030	3,910	3,830
24.5	160	281	3	4,210	4,090	4,000
25	160	281	3	4,320	4,190	4,100
25.5	165	286	3	4,470	4,340	4,250
26	165	286	3	4,610	4,470	4,380
26.5	165	286	3	4,800	4,660	4,560
27	170	291	3	4,920	4,780	4,680
28	170	291	3	5,300	5,150	5,040
28.5	175	296	3	5,500	5,340	5,230
29	175	296	3	5,810	5,630	5,520
30	175	296	3	6,240	6,050	5,930



注文例

YTD 20

型番 直径(D)

切削条件 P.648



出荷日

Delivery

在庫品 卷末-7

ご希望によりPM6:00迄、当日出荷受付致します。

